



## TBSI Headstage Connector Guide

### W-Series

Part Number	Description	Rows	Pin Count	Pin Spacing	PDF
A70008	5 Ch. headstage female connector	2	8	33 mil	
A70010	mates w/ A70008	2	8	33 mil	
A11862	16 Ch. headstage female connector	1	10	50 mil	
A11449	mates w/ A11862	1	10	50 mil	
A9094	16 Ch. headstage female connector	2	18	25 mil	
A8784	mates w/ A9094	2	18	25 mil	
A9409	32 Ch. headstage female connector	2	36	25 mil	
A9707	mates w/ A9409	2	36	25 mil	

### M-Series

Part Number	Description	Rows	Pin Count	Pin Spacing	PDF
A8829	32 - 224 Ch. headstage female connector	2	36	25 mil	
A9707	mates w/ A8829	2	36	25 mil	

### T-Series

Part Number	Description	Rows	Pin Count	Pin Spacing	PDF
A11862	8 Ch. female electrode side	1	10	50 mil	
A11449	mates w/ A11862	1	10	50 mil	
A9709	8 Ch. male recorder side	1	12	25 mil	
A7563	mates w/ A9709	1	12	25 mil	
A8376	8 Ch. female electrode side	1	10	25 mil	
A8393	mates w/ A8376	1	10	25 mil	
A8783	16 Ch. electrode side	2	18	25 mil	
A8784	mates w/ A8783	2	18	25 mil	
A8811	16 Ch. recorder side	2	22	25 mil	
A8829	32 Ch. electrode side	2	36	25 mil	
A9707	mates w/ A8829	2	36	25 mil	
A8830	32 Ch. male recorder side	2	40	25 mil	
A70267	mates w/ A8830	2	40	25 mil	

### S-Series

Part Number	Description	Rows	Pin Count	Pin Spacing	PDF
A8783	Electrode side connector	2	18	25 mil	